

Finger Cot

NATURAL RUBBER 100% / Powder Free
PINK (ANTI-STATIC)



Good quality

Low price

Delivery free



Roll Type

SPECIFICATION

Roll Type

Part code	Size	Qty/Bag
FCNRPR-S	S	1,440
FCNRPR-M	M	1,440
FCNRPR-L	L	1,440

Straight type

Part code	Size	Qty/Bag
FCNRPS-S	S	1,440
FCNRPS-M	M	1,440
FCNRPS-L	L	1,440

Size

Size (mm)	S	M	L
Inner Ø	15	18	20
Thickness	0.10 ± 0.02		
Length	65 ± 3		

AUTO ROLL PROCESSING

- We don't use any powder (Coating method)
- We use automated machine rolling process. This technology replaces risk of conventional finger cots rolled by hands.

Price: 225 THB / Bag

(Save cost)
20-30%

We can support the certificate document: MSDS / ROHS10 / Specification Data Sheet



Surface Resistivity

Long Lasting ESD 10e9 ohms/square



Application

- For Optronic Industries
- For Precise Industries
- For ESD Controlled Industries
- Plastic Component Handling



Straight Type



One stop



On time



Free delivery
No MOQ



Easy

search
buy



Contact
☎ 1382