




Cable Specification

Cable	
-------	--



Signal Cable (30 V)
A Cable: Soft MVVS Flexible Mold
 Not in catalog

Section Area	Number of Cores
0.08mm ²	4, 5, 6, 8



Main Specifications	
Standard Acquired	ULAWM2405/ULAWM2464
Rated Voltage	300 V
Rated Temperature	80 °C
Flame Retardance	VW-1
Bending Radius (Outer Diameter) (mm)	4 (Fixed Parts) — (Moving Parts)
* This is a recommended value, not a guaranteed value	
[Features] NA3GH-28-8 is UL2464.	

Has a small diameter with excellent flexibility for a wide range of uses!

Section Area	Number of Cores	Finished Outer Diameter
D Cable AWG28 (0.08 mm ²)	4	4.1mm
	5	4.5mm
	6	4.9mm

Electrical Properties

Number of Cores	Connector		A Cable			D Cable		
	Rated Current (A or less)	Rated Voltage (V or less)	Section Area	Rated Voltage	Allowable Current A (30°C)	Section Area	Rated Voltage	Allowable Current A (30°C)
4	1 (2A or less / 12 VDC)	100	0.08mm ²	30V	2.2	AWG28 (0.08 mm ²)	300V	2.2
5					2			2.1
6					2			1.9
8					1.8			—

* The values are reference values, not guaranteed values.

MDH Connector Supporting Model Number Table

Shape Specification	Cable Type	Number of Cores	CN1	Component Page	CN2	Component Page
P	A/D	4	MP371-4	0330		
	A/D	5	MP371-5	0330		
	A/D	6	MP371-6	0330		
	A/D	8	MP371-8	0330		
S	A/D	4	MJ372-4	0330		
	A/D	5	MJ372-5	0330		
	A/D	6	MJ372-6	0330		
	A/D	8	MJ372-8	0330		
PP	A/D	4	MP371-4	0330	MP371-4	0330
	A/D	5	MP371-5	0330	MP371-5	0330
	A/D	6	MP371-6	0330	MP371-6	0330
	A/D	8	MP371-8	0330	MP371-8	0330
PS	A/D	4	MP371-4	0330	MJ372-4	0330
	A/D	5	MP371-5	0330	MJ372-5	0330
	A/D	6	MP371-6	0330	MJ372-6	0330
	A/D	8	MP371-8	0330	MJ372-8	0330
SS	A/D	4	MJ372-4	0330	MJ372-4	0330
	A/D	5	MJ372-5	0330	MJ372-5	0330
	A/D	6	MJ372-6	0330	MJ372-6	0330
	A/D	8	MJ372-8	0330	MJ372-8	0330

- MS Connector Included Cable
- MS Connector Included Cable (Drip-proof)
- JL04 Connector Included Cable
- JL05 Connector Included Cable
- NCS Connector Included Cable
- NJC Connector Included Cable
- NJW Connector Included Cable
- NR Connector Included Cable
- NRW Connector Included Cable
- NET Connector Included Cable
- PRC04 Connector Included Cable
- PRC03 Connector Included Cable
- PRC05 Connector Included Cable
- R03 Connector Included Cable
- R04 Connector Included Cable
- PLT Connector Included Cable
- HR10A Connector Included Cable
- XS2 Connector Included Cable
- DIN / Mini-DIN Connector Included Cable