

Shaft Supports - T-Shaped (Cast)

Standard / Side Slit / Wide Side Slit

■ Features: Standard Type allows the shaft to be secured easily. Suitable when lengthwise space is limited.

Standard

RoHS10

Type	Material	Surface Treatment	Accessory
SHTBT	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTBM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 2 pcs.
SHTBS	SUS304 Equivalent	-	Hex Socket Set Screw 1 pc. (SUS)
SHTBA	AC7A	Clear Anodize	-

Cast Characters

Part Number Type	No.	D	H	L	H1	T	L1	d	L2	A	S	B1	B2	B3	Set Screw M	Mass g	Unit Price			
																	SHTBT	SHTBM	SHTBS	SHTBA
SHTBT SHTBM SHTBS SHTBA	815	8	15		24				18		6				M4	29 (10)				
	1020	10	20	42	30	10	32	5.5	20	21					M4	46 (16)				
	1220	12			32				25	24	8	14	8	2	M4	49 (17)				
	1320	13							46						M4	46 (16)				
	1625	16	25	48	40		38		30	30	10				M6	72 (25)				
	2025	20			60	43		45	6.6						M6	153 (53)				
	2030	20	30	70	50		56		35	35					M6	178 (62)				
	2530	25			84	53	20	64	9	44	42	12			M6	201 (70)				
3030	30													M8	314 (109)					

⚠ Values in () are the mass for aluminum products.

Side Slit

RoHS10

Type	Material	Surface Treatment	Accessory
SHTCT	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTCM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHTCS	SUS304 Equivalent	-	Hex Socket Head Cap Screw 1 pc. (SUS)
SHTCA	AC7A	Clear Anodize	-

Cast Characters

Part Number Type	No.	D	H	L	H1	T	L1	d	L2	A	S	E	C	B1	B2	B3	Tightening Screw M	Mass g	Unit Price			
																			SHTCT	SHTCM	SHTCS	SHTCA
SHTCT SHTCM SHTCS SHTCA	815	8	15	52	22		40		28	26		9					M4	61(21)				
	1020	10	20	54	29		42		30	27		10					M4	81(28)				
	1220	12			56	31	12	44	5.5	32	28	6	11				M4	90(31)				
	1320	13								34	29		12				M4	87(30)				
	1625	16	25	58	37		46		34	29		12	2	14	8	2	M6	107(37)				
	2025	20			79	40		64	6.5	49	39.5	8	17				M6	220(76)				
	2030	20	30	79	45	16	64	6.5	49	39.5	8	17				M6	254(88)					
	2530	25			102	48		82	9	62	51	10	18				M8	248(86)				
3030	30															M8	477(165)					

⚠ Values in () are the mass for aluminum products.

Wide Side Slit

RoHS10

Type	Material	Surface Treatment	Accessory
SHTCTN	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTCMN	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 2 pcs. (SUS)

Cast Characters

Part Number Type	D	H	L	H1	T	T1	L1	d	L2	S	E	C	Tightening Screw M	d1	d2	ℓ	Weight g	Unit Price		
																		SHTCTN	SHTCMN	
SHTCTN SHTCMN	10	20	62	30	20	-	50		38	6	12		M6	11	6.6	6.5	181			
	12			38	25						12.5		M6				176			
	16	25											M8				264			
	20			85	48	30	15	70	6.6	58	8	20.5		M8	14	9	9	614		
	25	30								70	10	24	3	M8				574		
30			110	53	40	20	90						M8				1038			

Ordering Example
Part Number
SHTBT3030
SHTCS2025
SHTCTN20

Shaft Supports - T-Shaped Split (Cast)

Standard / Wide

■ Features: Shaft Supports are removable and thus, facilitate maintenance. Wide Type has a long shaft holding section and has enhanced gripping power.

Standard

RoHS10

Type	Material	Surface Treatment	Accessory
SHTDT	S45C	Black Oxide	Hex Socket Head Cap Screw 2 pcs.
SHTDM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 2 pcs.
SHTDA	AC7A	Clear Anodize	Hex Socket Head Cap Screw 2 pcs. (SUS)

Cast Characters

Part Number Type	No.	D	H	L	H1	T	L1	d	L2	A	S	E	C	B1	B2	B3	Tightening Screw M	Mass g	Unit Price		
																			SHTDT	SHTDM	SHTDA
SHTDT SHTDM SHTDA	815	8	15	52	22		40		28	26		18					M4	58 (20)			
	1020	10	20	54	29		42		30	27		20					M4	78 (27)			
	1220	12			56	31	12	44	5.5	32	28	6	22				M4	87 (30)			
	1320	13								34	29		24				M4	84 (29)			
	1625	16	25	58	37		46		34	29		24	2	14	8	2	M6	104 (36)			
	2025	20			79	40		64	6.5	49	39.5	8	34				M6	214 (74)			
	2030	20	30	79	45	16	64	6.5	49	39.5	8	34					M6	249 (86)			
	2530	25			102	48		82	9	62	51	10	44	3			M8	243 (84)			
	3030	30															M8	463 (160)			

⚠ Values in () are the mass for aluminum products.

Wide Split

RoHS10

Type	Material	Surface Treatment	Accessory
SHTDTN	S45C	Black Oxide	Hex Socket Head Cap Screw 2 pcs.
SHTDMN	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 2 pcs. (SUS)

Cast Characters

Part Number Type	D	H	L	H1	T	T1	L1	d	L2	S	E	C	Tightening Screw M	d1	d2	ℓ	Mass g	Unit Price		
																		SHTDTN	SHTDMN	
SHTDTN SHTDMN	10	20	62	30	20	-	50		38	6	24		M6	11	6.6	6.5	177			
	12			38	25						25		M6				172			
	16	25											M8				260			
	20			85	48	30	15	70	6.6	58	8	41		M8	14	9	9	605		
	25	30								70	10	48	3	M8				566		
30			110	53	40	20	90						M8				1019			

Ordering Example
Part Number
SHTDT1320
SHTDA2030
SHTDMN25