

Knurled Knobs with Captured Washer

Type	Knobs	Flat Washer
NKOST	SUS303 Brushed Finish	SUS303

NKOST

Part Number		M (Coarse)		L Selection		D	d	A	H	S	D ₁	t	Unit Price	
NKOST	Type	6	10	16	20	25	24	12	5	15	10	14.5	1.5	
		8	16	20	25	30	30	16	6	18	12	20	2	
		10	20	25	30	40	36	20	8	23	15	25	2.5	

Stepped Knobs - No Knurling

Type	Material
NKCR	SUS303

NKCR

Part Number		M (Coarse)		L Selection		D	d	A	H	S	ℓ	Unit Price	
NKCR	Type	3	6	10		12	6	2.5	7.5	5	1		
		4	10	16		16	8	3.5	9.5	6	1.2		
		5	10	16		20	10	4	11.5	7.5	1.4		
		6	16	20		24	12	5	15	10	1.5		

Knurled Knobs - Large Diameter

Type	Material	Surface Treatment
Standard Stepped NORD/NKRD	SUM23	Buff Polished + Chrome Plating

Part Number		M (Coarse)		L Selection		d	A	R	H	h	S	ℓ	Unit Price		
														NORD	NKRD
Standard Stepped	Type	5	16	25		10	8	2.5	15.5	2.5	7.5	1.4			
		6	16	30		12	10	3	20	3	10	1.5			
		8	16	30		16	12	4	24	4	12	2			

Knurled Knobs - Small Diameter

Type	Shape	Material	Surface Treatment
Standard Stepped NOBC/NKBC	Threaded	SUM23	Buff Polished + Chrome Plating
NOSC/NKOSC		SUS303	Brushed Finish
NOMC/NKMC	Tapped	SUM23	Buff Polished + Chrome Plating
NOMSC/NKMSC		SUS303	-

Part Number		M (Coarse)		L Selection (Threaded Type only)		D Selection		d	A	T	H	S	ℓ	Unit Price				
														NOBC/NKBC	NOSC/NKOSC	NOMC/NKMC	NOMSC/NKMSC	
Standard NOBC NOSC NOMC NOMSC	Stepped NKBC NKOSC NKMC NKMSC	3	6	10		*5	8	10	6	2.5	3	7.5	5	1				
		4	6	10	16		*7	12	14	8	3.5	4	9.5	6	1.2			
		5	10	16	20		*12	16	18	10	4	5	11.5	7.5	1.4			
		6	10	16	20	25	30	*13	20	22	12	5	6	15	10	1.5		
		8	16	20	25	30	40	*17	26	28	16	6	8	18	12	2		
		10	20	25	30	40		*20	30	32	20	8	10	23	15	2.5		

* marked items are applicable to NOBC and NOSC only.

Ordering Example: Part Number - L - D

NKOST6 - 25
NKCR3 - 10
NORD8 - 30
NOBC5 - 10 - 18

Knurled Knobs with Hex Socket

Type	Material	Surface Treatment
Standard Stepped NOBR/NKBR	SUM24L	Buff Polished + Chrome Plating
NOOSR/NKOSR	SUS303	Brushed Finish

Part Number		M (Coarse)		L Selection		A	D	d	H	S	ℓ	B	Unit Price		
														NOBR/NKBR	NOOSR/NKOSR
Standard Stepped NOBR NOOSR	Type	3	6	10		12	12	6	17	5	1	2			
		4	6	10	16		17	16	8	23	6	1.2	2.5		
		5	10	16	20		26	20	10	33.5	7.5	1.4	3		

Ordering Example: Part Number - L

NOBR3 - 6

Checker Knurled Knobs

Type	Shape	Material	Surface Treatment
Standard Stepped NOBX/NKBX	Threaded	SUM24L	Buff Polished + Chrome Plating
NOOSX/NKOSX		SUS303	Brushed Finish
NOMSX/NKMSX	Tapped	SUS303	Brushed Finish

Part Number		M (Coarse)		L Selection (Threaded Type only)		A	D	d	T	H	S	ℓ	Unit Price			
														NOBX/NKBX	NOOSX/NKOSX	NOMSX/NKMSX
Standard Stepped NOBX NOOSX NOMSX	Type	3	6	10		10	12	6	11	15	5	1				
		4	6	10	16		11	16	8	12	17	6	1.2			
		5	10	16	20		12	20	10	13	19.5	7.5	1.4			

Knurled Knobs - Captured

Type	Material	Surface Treatment
Standard Stepped NOBD/NKBD	SUM24L	Buff Polished + Chrome Plating
NOOSD/NKOSD	SUS303	Brushed Finish

There may be uneven chrome plating around the threads.

Part Number		M (Coarse)		L	D	d	A	H	S	ℓ	d ₂	Unit Price	
												NOBD/NKBD	NOOSD/NKOSD
Standard Stepped NOBD NOOSD	Type	3	10	12	6	2.5	7.5	5	6	2			
				10	16	8	3.5	9.5	6	5	3		
				15	10								
		5	15	20	10	4	11.5	7.5	9	3.8			
				20									
				14									
		6	20	24	12	5	15	10	12	4.5			
				30									
				22									
		8	30	20	16	6	18	12	10	6			
				20									

Example

Ordering Example: Part Number - L

NOBX3 - 6
NOBD5 - 10