

Dowel Pins

Oversized

One End Tapped

Type	Material	Hardness
MSTP	SUJ2	58HRC~
MSTPC	SUS440C	58HRC~
MSTPCS	SUS304	-

Air Vent Depth
All air vents are identical in depth.
0.15 ±0.05

- When D=5 or 6 and L=10, the pilot hole for tapping may go through.
- * l=6 only when D=6 and L=10
- l1 dimension may become larger than the value shown in the catalog due to polishing process.

l1	MxP	l	Part Number		L	Unit Price	Volume Discount Rate
			Type	D			
1.5	3x0.5	6	MSTP	5	10 15 20 25 30		
				6	20 30		
2.0	4x0.7	*8	MSTP	6	10 15 25 35 40 50		
				8	30		
2.0	5x0.8	*8	MSTP	8	15 20 25 35 40 45 50 60		
				10	40		
2.5	6x1.0	10	MSTP	10	15 20 25 30 35 45 50 60 70		
				12	80		
2.5	8x1.25	15	MSTP	12	20 30 40 50 60 70		
				13	80		
3.0	8x1.25	15	MSTP	13	50		
				16	40 60 70		

For orders larger than indicated quantity, please check with WOS.

l1	MxP	l	Part Number		L	Unit Price	Volume Discount Rate
			Type	D			
1.5	3x0.5	6	MSTPC	5	10 15 20		
				6	15 20 25 30		
2.0	4x0.7	8	MSTPC	8	15 20 25 30 35 40		
				10	20 25 30 35 40 45 50 60		
2.5	6x1.0	10	MSTPC	12	30 40 50 60		
				13	30 40 50 60		

For orders larger than indicated quantity, please check with WOS.

l1	MxP	l	Part Number		L	Unit Price	Volume Discount Rate
			Type	D			
1.5	3x0.5	6	MSTPCS	5	10 15 20 25 30		
				6	10 15 20 25 30 35 40		
2.0	4x0.7	8	MSTPCS	8	15 20 25 30 35 40 45 50		
				10	20 25 30 35 40 45 50		

For orders larger than indicated quantity, please check with WOS.

One End Tapped (Hollow)

Type	Material	Hardness
THS	SUJ2	45~50HRC
THSS	SUS440C	45~50HRC

For orders larger than indicated quantity, please check with WOS.

l1	l2	l	MxP	Dp6	Part Number		L	Unit Price	Volume Discount Rate
					Type	D			
2	0.3	8	4x0.7	+0.020 +0.012	THS	6	15 20 25 30 35		
						8	15 20 25 30 35		
2.5	0.5	10	5x0.8	+0.024 +0.015	THS	10	20 25 30 35 40		
						12	20 25 30 35 40 45		

For orders larger than indicated quantity, please check with WOS.

l1	l2	l	MxP	Dp6	Part Number		L	Unit Price	Volume Discount Rate
					Type	D			
2	0.3	8	4x0.7	+0.020 +0.012	THSS	6	15 20 25 30 35		
						8	15 20 25 30 35		
2.5	0.5	10	5x0.8	+0.024 +0.015	THSS	10	20 25 30 35 40		
						12	20 25 30 35 40 45		

For orders larger than indicated quantity, please check with WOS.

One End Tapped

Type	D Tolerance	Material	Hardness
MST	p6	SUJ2	45~50HRC
MSTM	m6	SUS440C	45~50HRC
MSTMS	m6	SUS440C	45~50HRC

Air Vent Depth
All air vents are identical in depth.
0.15 ±0.05

- When D=5 or 6 and L=10, the pilot hole for tapping may go through.
- * l=6 only when D=6 and L=10
- l1, l2 dimension may become larger than the value shown in the catalog due to polishing process.

l1	l2	MxP	l	Dp6	Part Number		L	Unit Price	Volume Discount Rate
					Type	D			
1.5	0.3	3x0.5	6	+0.020 +0.012	MST	5	10 15 20 25 30		
						6	20 30		
2.0	0.5	4x0.7	*8	+0.024 +0.015	MST	6	10 15 25 35 40 50		
						8	30		
2.5	1.0	6x1.0	10	+0.029 +0.018	MST	10	15 20 25 30 35 45 50 60 70		
						12	80		
3.0	1.5	8x1.25	15	+0.035 +0.022	MST	13	50		
						16	40 60 70		
3.0	1.5	10x1.5	18	+0.035 +0.022	MST	20	40 50 60 70 80		
						20	50 60 70 80		

For orders larger than indicated quantity, please check with WOS.

l1	l2	MxP	l	Dm6	Part Number		L	Unit Price	Volume Discount Rate
					Type	D			
1.5	0.3	3x0.5	6	+0.012 +0.004	MSTM	5	10 15 20 25 30		
						6	20 30		
2.0	0.5	4x0.7	*8	+0.015 +0.006	MSTM	8	10 15 25 35 40 50 60		
						10	30		
2.5	1.0	6x1.0	10	+0.018 +0.007	MSTM	10	15 20 25 30 35 45 50 60 70		
						12	80		
3.0	1.5	8x1.25	15	+0.021 +0.008	MSTM	13	50		
						16	40 60 70		
3.0	1.5	10x1.5	18	+0.021 +0.008	MSTM	20	60		
						20	40 50 70 80		

For orders larger than indicated quantity, please check with WOS.

l1	l2	MxP	l	Dm6	Part Number		L	Unit Price	Volume Discount Rate
					Type	D			
1.5	0.3	3x0.5	6	+0.012 +0.004	MSTMS	5	10 15 20		
						6	20 30		
2.0	0.5	4x0.7	*8	+0.015 +0.006	MSTMS	8	10 15 25 30		
						10	30		
2.0	0.5	5x0.8	*8	+0.015 +0.006	MSTMS	8	15 20 25 35 40		
						10	20 25 30 35		

For orders larger than indicated quantity, please check with WOS.

Tapered, Tapped

Type	Material	Hardness
MTT	SK95 Equivalent	45~50HRC

For orders larger than indicated quantity, please check with WOS.

MxP	l	Part Number		L	Unit Price	Volume Discount Rate
		Type	D			
5x0.8	9	MTT	8	30 40		
			10	40 50		
6x1.0	10	MTT	12	40 50		
			13	50 60		
8x1.25	14	MTT	13	50 60		
			16	60 70		

For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number - L

MSTP5 - 10

MSTMS6 - 20

For orders larger than indicated quantity, please check with WOS.
For orders larger than indicated quantity, please request a quotation. P.99