

# Accessory Parts

**RoHS10**

Part Number	Material	Surface Treatment
JBS201	SUS303	-
JBS301	SPCC	Trivalent Chromate
FFS102	SPCC	Trivalent Chromate
JBS306	SPHC	-
JBS402	Polychloroprene	-
JBS403	Styrene-butadiene Rubber	-

**Frame Jointing Fitting** JBS201  
**Saddles with One Fixing** JBS301 (Set of 4)  
**Saddles with Two Fixings** FFS102 (Set of 4)  
**JBS306**  
**Inner Rubber Cap** JBS402  
**Outer Rubber Cap** JBS403

Part Number	Mass (g)	Unit Price
JBS201	59	
JBS301	19	
FFS102	24	
JBS306	28	
JBS402	15	
JBS403	31	

\* JBS301 and FFS102 is in set of 4 pieces.

**RoHS10**

Part Number	Material	Surface Treatment
JBS601	Polyester	-
JBS601S		
JBS611		
JBS612		
FFS106	SS400	Chrome Plating

**Name Holder** JBS601  
**Name Holder** JBS601S  
**Name Holder** JBS611  
**Name Holder** JBS612  
**Ring Slider** FFS106 (Set of 10)

Part Number	Mass (g/pc.)	Unit Price
JBS601	34	
JBS601S	16	
JBS611	49	
JBS612	41	
FFS106	14	

Example:

# Adjusting Bolts

Part Number	Material	Surface Treatment
JBS202	SPCC	Trivalent Chromate
JBS401	Polypropylene	-
JBS404	SPCC	Trivalent Chromate
JBS405		
JBS406	Plastic Styrene-butadiene Rubber	-
JBS407	AAS Resin	-

**Adjuster** JBS401  
**Adjusting Bolt A set** JBS404  
**Adjusting Bolt B set** JBS405  
**Insert Nut** JBS406  
**Pipe Stand S** JBS202  
**Inner Stand** JBS407  
**Inner Stand** JBS408

Unavailable for aluminum pipe frames

Stroke: 20mm

Adjustment Range: 40mm

Adjustment Range: 50mm

Part Number	Color	Mass (g)	Unit Price
JBS202	-	302	
JBS401	W, S	35	
JBS404	-	330	
JBS405	-	305	
JBS406	-	75	
JBS407	-	126	
JBS408	W (White)	92	

Ordering Example: Part Number - Color  
 JBS202  
 JBS401 - W

## Insert Nut - Stainless Steel

**PFINS**

Tapered part from tip to head (1.2°) allows insertion into the I.D. of pipe frames.

Material: Stainless Steel

Part Number	Mass (g)	Unit Price
PFINS	89	
	85	
	82	

Ordering Example: Part Number  
 PFINS10

Can be used for Standard Leveling Mounts (P.1107).