

■ Part numbers subject to specification changes

No.	Type	Part Number	No.	Type	Part Number	No.	Type	Part Number
1	Straigh Type	ROFAWC30-12	41	Crowned Type	ROFAWT30-12	81	V-Groove Straight Type	ROFAWM30-12
2		ROFAWC35-12	42		ROFAWT35-12	82		ROFAWM35-12
3		ROFAWC35-15	43		ROFAWT35-15	83		ROFAWM35-15
4		ROFAWC40-8	44		ROFAWT40-8	84		ROFAWM40-8
5		ROFAWC40-12	45		ROFAWT40-12	85		ROFAWM40-12
6		ROFAWC40-15	46		ROFAWT40-15	86		ROFAWM40-15
7		ROFAWC40-20	47		ROFAWT40-20	87		ROFAWM40-20
8		ROFAWC50-10	48		ROFAWT50-10	88		ROFAWM50-10
9		ROFAWC50-15	49		ROFAWT50-15	89		ROFAWM50-15
10		ROFAWC50-20	50		ROFAWT50-20	90		ROFAWM50-20
11		ROFAWC50-25	51		ROFAWT50-25	91		ROFAWM50-25
12		ROFAWC60-12	52		ROFAWT60-12	92		ROFAWM60-12
13		ROFAWC60-15	53		ROFAWT60-15	93		ROFAWM60-15
14		ROFAWC60-20	54		ROFAWT60-20	94		ROFAWM60-20
15		ROFAWC60-25	55		ROFAWT60-25	95		ROFAWM60-25
16		ROFAWC60-30	56		ROFAWT60-30	96		ROFAWM60-30
17		ROFAWC80-25	57		ROFAWT80-25	97		ROFAWM80-25
18		ROFAWC80-35	58		ROFAWT80-35	98		ROFAWM80-35
19		ROFMWC30-12	59		ROFMWT30-12	99		ROFMWM40-8
20		ROFMWC35-12	60		ROFMWT35-12	100		ROFMWM40-12
21		ROFMWC35-15	61		ROFMWT35-15	101		ROFMWM40-15
22		ROFMWC40-8	62		ROFMWT40-8	102		ROFMWM40-20
23		ROFMWC40-12	63		ROFMWT40-12	103		ROFMWM50-10
24		ROFMWC40-15	64		ROFMWT40-15	104		ROFMWM50-15
25		ROFMWC40-20	65		ROFMWT40-20	105		ROFMWM50-20
26		ROFMWC50-10	66		ROFMWT50-10	106		ROFMWM50-25
27		ROFMWC50-15	67		ROFMWT50-15	107		ROFSWM40-8
28		ROFMWC50-20	68		ROFMWT50-20	108		ROFSWM40-12
29		ROFMWC50-25	69		ROFMWT50-25	109		ROFSWM40-15
30		ROFSWC30-12	70		ROFSWT30-12	110		ROFSWM40-20
31		ROFSWC35-12	71		ROFSWT35-12	111		ROFSWM50-10
32		ROFSWC35-15	72		ROFSWT35-15	112		ROFSWM50-15
33		ROFSWC40-8	73		ROFSWT40-8	113		ROFSWM50-20
34		ROFSWC40-12	74		ROFSWT40-12	114		ROFSWM50-25
35		ROFSWC40-15	75		ROFSWT40-15			
36		ROFSWC40-20	76		ROFSWT40-20			
37		ROFSWC50-10	77		ROFSWT50-10			
38		ROFSWC50-15	78		ROFSWT50-15			
39		ROFSWC50-20	79		ROFSWT50-20			
40	ROFSWC50-25	80	ROFSWT50-25					