

Cable Clamps

Cable Clamps - Diamond Shape

HFCN5 PACK
(50 pcs./pkg.)

HFCN6 PACK
(50 pcs./pkg.)

HFCN8 PACK
(50 pcs./pkg.)

Material: Polyamide (Light Gray) RoHS10
 The photo is of HFCN8. Attachable by hand.

Part Number	Extrusion (Series)	Unit Price	Volume Discount Rate
Type	No.	1 ~ 2 pkg(s).	3~30
HFCN	5PACK	HFS5	
	6PACK	HFS6	
	8PACK	HFS8 HFS8-45	

50 pcs. per pkg. When ordering, please note the quantity. 300 pcs. will be delivered for an order of one HFCN5PACK-SET.

Cable Clamps - Circular

HFCC5 PACK
(50 pcs./pkg.)

HFCC6 PACK
(50 pcs./pkg.)


HFCC8 PACK
(50 pcs./pkg.)

Material: Polyamide (Light Gray) RoHS10
 The photo is of HFCC8. Attachable by hand.

Part Number	Extrusion (Series)	Unit Price	Volume Discount Rate
Type	No.	1 ~ 2 pkg(s).	3~30
HFCC	5PACK	HFS5	
	6PACK	HFS6	
	8PACK	HFS8 HFS8-45	

When using No. 8 for HFS8-45, the fit becomes slightly firmer. When ordering, please note the quantity. 300 pcs. will be delivered for an order of one HFCC5PACK-SET.
 50 pcs. per pkg.

Ordering Example Part Number **HFCC6PACK**



Cable Covers

Cable Covers

HSCE (Standard Length)

HSCEF (Configurable Length)

Material: Polypropylene Resin RoHS10


Cable Covers Standard Length

Part Number	Color	L m	Applicable Extrusion (Series)	Unit Price	Volume Discount Rate
Type	No.			1 ~ 5 pc(s).	6~20
HSCE	S (Light Gray)	2	HFS8		

Cable Covers Configurable Length

Part Number	Color	L 1mm Increment	Applicable Extrusion (Series)	Unit Price/m
Type	No.			1 ~ 20 pc(s).
HSCEF	S (Light Gray)	100~2000	HFS8	

Unit Price/m x Specified Full Length = Price




Cable Cover L-Shaped Connectors

HSCELA (Vertical L-shaped)

HSCELB (Flat L-shaped)

Material: ABS Resin RoHS10

Part Number	Color	Unit Price	Volume Discount Rate
Type	No.	1 ~ 5 pc(s).	6~20
HSCELA HSCELB	S (Light Gray)		



Ordering Example Part Number - Color - L
HSCE8 - S - 2
HSCELB8 - S