

# Safety Mesh Fence Units

**HFUA** (Silver Type)  
**HFUAY** (Yellow Type)  
**K-HFUA** (Silver Type, Assembly & Shipping Service)  
**K-HFUAY** (Yellow Type, Assembly & Shipping Service)

Units without "K-" in the part number require customer assembly.  
 For details of Mesh Fence, see **P.943**.  
 For (A) part, refer to Alterations below.

RoHS 10

**Silver Type**

Part Number	Mesh Fence (Wire Ø3.2) Panel (t=3) Selection	W (Width) 1mm Increment	D (Height) 1mm Increment	H (Leg Height) Selection	T	Components			
						Mesh Fence Parts	Extrusion Parts	Fastening Parts	Quantity
<b>HFUA</b> <b>K-HFUA</b>	6 30B (Pitch 30mm, Black) 30S (Pitch 30mm, Silver) 50B (Pitch 50mm, Black) 50S (Pitch 50mm, Silver)	300 1000	500 1030	0 150	30 40	Black (FENP) Silver (FENM)	HFFS6-3030 HFFS8-4040	SCB8-40 SCB12-60	4 4
	PET3 (PET 3mm, Clear) AC3 (Acrylic 3mm, Clear) PC3 (Polycarbonate 3mm, Clear) ST3 (Anti-static PVC 3mm, Clear)								

**Yellow Type**

Part Number	Mesh Fence (Wire Ø3.2) Panel (t=3) Selection	W (Width) 1mm Increment	D (Height) 1mm Increment	H (Leg Height) Selection	T	Components			
						Mesh Fence Parts	Extrusion Parts	Fastening Parts	Quantity
<b>HFUAY</b> <b>K-HFUAY</b>	6 30B (Pitch 30mm, Black) 30S (Pitch 30mm, Silver) 50B (Pitch 50mm, Black) 50S (Pitch 50mm, Silver)	300 1000	500 1030	0 150	30 40	Black (FENP) Silver (FENM)	HFFSY6-3030 HFFSY8-4040	SCB8-40 SCB12-60	4 4
	PET3 (PET 3mm, Clear) AC3 (Acrylic 3mm, Clear) PC3 (Polycarbonate 3mm, Clear) ST3 (Anti-static PVC 3mm, Clear)								

**Ordering Example**

Part Number - Mesh Fence - W - D - H

HFUA6 - 30B - W700 - D800 - H150  
 K-HFUA6 - 30B - W700 - D800 - H150

**Alterations**


Part Number - Mesh Fence - W - D - H - (Alteration Code)

HFUA6 - 30B - W700 - D800 - H150 - UTP  
 K-HFUA6 - 30B - W700 - D800 - H150 - UTP

Alteration	Code	Spec.
Tapping on the Bottom End Face	UTP	Adds tapped holes on (A) in the drawing. HFUA6, HFUAY6 ⇒ M8 Depth 24 HFUA8, HFUAY8 ⇒ M12 Depth 36

**EX** Example <Features of Extrusions for Safety Mesh Fences>  
 Slot profile is the same as that of aluminum extrusion HFS series except the dedicated slot for the mesh fence.  
 All other accessories for the HFS Series (nuts, extrusion end caps, etc.) can be used.

**How to Assemble**



**HFUB** (Silver Type)  
**HFUBY** (Yellow Type)  
**K-HFUB** (Silver Type, Assembly & Shipping Service)  
**K-HFUBY** (Yellow Type, Assembly & Shipping Service)

Units without "K-" in the part number require customer assembly.  
 For details of Mesh Fence, see **P.943**.  
 For (A) part, refer to Alterations below.

RoHS 10

**Silver Type**

Part Number	Mesh Fence (Wire Ø3.2) Panel (t=3) Selection	W (Width) 1mm Increment	D (Height) 1mm Increment	H (Leg Height) Selection	T	Components			
						Mesh Fence Parts	Extrusion Parts	Fastening Parts	Quantity
<b>HFUB</b> <b>K-HFUB</b>	6 30B (Pitch 30mm, Black) 30S (Pitch 30mm, Silver) 50B (Pitch 50mm, Black) 50S (Pitch 50mm, Silver)	300 1000	1000 2200	0 150	30 40	Black (FENP) Silver (FENM)	HFFS6-3030 HFFH6-3030 HFFS8-4040 HFFH8-4040	SCB8-40 SCB12-60	6 6
	PET3 (PET 3mm, Clear) AC3 (Acrylic 3mm, Clear) PC3 (Polycarbonate 3mm, Clear) ST3 (Anti-static PVC 3mm, Clear)								

**Yellow Type**

Part Number	Mesh Fence (Wire Ø3.2) Panel (t=3) Selection	W (Width) 1mm Increment	D (Height) 1mm Increment	H (Leg Height) Selection	T	Components			
						Mesh Fence Parts	Extrusion Parts	Fastening Parts	Quantity
<b>HFUBY</b> <b>K-HFUBY</b>	6 30B (Pitch 30mm, Black) 30S (Pitch 30mm, Silver) 50B (Pitch 50mm, Black) 50S (Pitch 50mm, Silver)	300 1000	1000 2200	0 150	30 40	Black (FENP) Silver (FENM)	HFFSY6-3030 HFFHY6-3030 HFFSY8-4040 HFFHY8-4040	SCB8-40 SCB12-60	6 6
	PET3 (PET 3mm, Clear) AC3 (Acrylic 3mm, Clear) PC3 (Polycarbonate 3mm, Clear) ST3 (Anti-static PVC 3mm, Clear)								

**Ordering Example**

Part Number - Mesh Fence - W - D - H

HFUBY8 - 50B - W800 - D1800 - H150  
 K-HFUBY8 - 50B - W800 - D1800 - H150

**Alterations**

Part Number - Mesh Fence - W - D - H - (Alteration Code)

HFUBY8 - 50S - W800 - D1800 - H150 - UTP  
 K-HFUBY8 - 50S - W800 - D1800 - H150 - UTP

Alteration	Code	Spec.
Tapping on the Bottom End Face	UTP	Adds tapped holes on (A) in the drawing. HFUB6, HFUBY6 ⇒ M8 Depth 24 HFUB8, HFUBY8 ⇒ M12 Depth 36

**EX** Example <How to Mount Safety Fence Extrusions>

