




Simplified Slide Rails Load Rating: 28, 110N / pc. 177~235 N / 2 pcs, Aluminum, Lubrication-Free / Stainless Steel, Compact

■ **Features:** For Aluminum Type, plastic sliders are used for lubrication-free operation. Stainless Steel Type is compact and suitable for space-saving designs.




Type		Part	Material	Surface Treatment	
Set (Slider 1 pc. + Rail 1 pc.)	No Stopper / With Stopper				
SROM (Tapped Hole Type)	SROMST (Tapped Hole Type)	(1) Rail	Aluminum Alloy	Clear Anodize	
		(2) Slider	Polyacetal	-	
	SROZ (Counterbored Type)	SROZST (Counterbored Type)	(3) Slider	C3604 Equivalent	-
			(4) Retainer	Aluminum Alloy	-
		(5) Stopper	Aluminum Alloy	Clear Anodize	
		(6) Set Screw	Stainless Steel	-	

⚠ To prevent the slider fall-off, select with-stopper type.






■ **Features:** Sliders are made of polyacetal resin with a strong sliding property, enabling maintenance-free operation.






<Stopper>
Retaining stopper can be mounted at any position on the rail.

- ⚠ Clearance between a rail and a slider is approximately 0.3 to 0.9 mm.
- ⚠ Use in places where guides are subjected to moment load is not recommended.
- ⚠ SROMST and SROZST (with stoppers) include 2 stoppers each.
- ⚠ For installation of rails, use Hex Socket Extra Low Head Cap Screw (P.2-269) or Nut (P.2-269).



- **Features:** Can be used for various applications as designed to reduce deflection with 15.5mm in height.
- ⚠ * marked holes are not provided for Rail Length 80mm Type.
 - ⚠ Do not apply a strong impact to any rail stopper or any retainer.
 - ⚠ To install outer rails, use M2.6 low head screws (Head Dia.: 4.0, Head Height: 0.9mm).
 - ⚠ To install inner rails, use M2.6 machine screws (Thread Length ≤ (Mounting Plate Thickness) + 1.5mm).



Part Number	Type	L No.	Mounting Number of Holes	Effective Stroke	Slider 1 pc.	Load Rating	Unit Price	
							(No Stopper) ¹⁾	(With Stopper) ²⁾
90	Tapped Hole SROM (No Stopper) SROMST (With Stopper)	2	64	44	28(3)	N/kgf / 2 pcs. 177(18)	SROM15	SROM15
140		3	114	94				
190		4	164	144				
240		5	214	194				
290		6	264	244				
340		7	314	294				
390		8	364	344				
440		9	414	394				
490		10	464	444				
540		11	514	494				
590		12	564	544				
640		13	614	594				
690		14	664	644				
740		15	714	694				
790		16	764	744				
840		17	814	794				
890		18	864	844				
940	19	914	894					
990	20	964	944					
1040	21	1014	994					

Part Number	Type	L No.	Mounting Number of Holes	Effective Stroke	Slider 1 pc.	Load Rating	Unit Price			
							(No Stopper) ¹⁾	(With Stopper) ²⁾	SROM25	SROZ25
90	Tapped Hole SROM (No Stopper) SROMST (With Stopper) Counterbored SROZ (No Stopper) SROZST (With Stopper)	2	52	62	110(11)	N/kgf / 2 pcs. 177(18)				
140		3	102	62						
190		4	152	112						
240		5	202	162						
290		6	252	212						
340		7	302	262						
390		8	352	312						
440		9	402	362						
490		10	452	412						
540		11	502	462						
590		12	552	512						
640		13	602	562						
690		14	652	612						
740		15	702	662						
790		16	752	712						
840		17	802	762						
890		18	852	812						
940	19	902	862							
990	20	952	912							
1040	21	1002	962							

Part Number	L	Mounting	Effective	A	B	C	D	E	F	G	H	Load Rating	Unit Price	Volume Discount Rate
Type	No.	Selectable	Stroke									N/kgf / 2 pcs.	1-5 pcs(s).	6-20 pcs.
80	4	49	28	18	-	-	-	56	-	32	177(18)			
100	5	59	38	28	6	12	10	76	38	52	206(21)			
150	5	109	38	28	6	12	10	126	63	102	235(24)			
200	5	149	48	38	10	14	14	176	88	152				

- ⚠ *1. Effective stroke (No Stopper) is the dimension value with a margin of approx. 3mm set from each end to avoid dropout of sliders.
- ⚠ *2. Effective stroke (With Stopper) is the dimension value with a margin of approx. 3mm set from contacts of sliders and stoppers to avoid conflict between them.
- ⚠ Maximum Allowable Speed is 0.85m/sec

Ordering Example
Part Number - L
SROM15 - 1040
SROZ25 - 540
MSCRL2 - 150

Alterations Part Number - L - (T, Z)
SROM25 - 540 - T2

Alterations	Code	Spec.
Tapped Hole Type	T	Sliders are added. Please specify additional slider quantity after T and Z. ■ Selection Example
Additional Slider	Z	Additional Slider Qty. Tapped Hole Counterbored Hole Ordering Code Slider Total Qty.
		5 0 SROM25-540-T5 6
		1 2 SROM25-540-T1-Z2 4

⚠ Added sliders are the same size as that of the original part number model.
⚠ No.15 L≥20 x Slider Total Qty.
⚠ No.25 L≥32 x Slider Total Qty.
⚠ Possible to add up to 10 pcs.