


# TUBES

-(MAXIMUM 60°C)-



Material	Outer x Inner dia.	Max. pressure MPa (kgf/cm <sup>2</sup> )	Usable temp. range (°C)	Part Number		Length (m)	Tube color		Unit Price
				Type	No.				
Poly urethane (PU resin)	3x2	0.99 (9.9)	32~140°F/ 0~60°C	K-M-PU	0302	20	Black Red Blue Yellow Green Transparent	BK RD BU YL GR CL	Quotation
	4x2				0402				
	4x2.5				0425				
	6x4				0604				
	8x5				0805				
	10x6.5				1065				
	12x8				1208				
16x11	1611								



Material	Outer x Inner dia.	Max. pressure MPa (kgf/cm <sup>2</sup> )	Usable temp. range (°C)	Part Number		Length (m)	Tube color		Unit Price
				Type	No.				
Poly Ethylene (PE resin)	4x2.5	0.99 (9.9)	32~140°F/ 0~60°C	K-M-PE	0425	20	White Red	WT RD	Quotation
	6x4				0604				
	8x6				0806				
	10x7				1007				
	12x9				1209				



Material	Outer x Inner dia.	Max. pressure MPa (kgf/cm <sup>2</sup> )	Usable temp. range (°C)	Part Number		Length (m)	Tube color		Unit Price
				Type	No.				
Poly Amid (PA resin)	4x2.5	0.99 (9.9)	32~140°F/ 0~60°C	K-M-PA	0425	20	White Black	WT BK	Quotation
	6x4				0604				
	8x6				0806				
	10x7				1007				
	12x9				1209				



Order

Part Number	Length	Tube color
K-M-PU-0302	20	BK
K-M-PE-0425	20	WT
K-M-PA-0425	20	WT



Days to Ship

**Quotation**



Price

**Quotation**