



CYLINDER BRUSH (CARBON STEEL / BRASS) / EXTENSION SHAFT

shows in red

■ Application Use for cleaning cylinders.



■ Features

- It is used for cleaning hardened cylinders.
- It is made specially to clean cylinder of molding machines and it does not scratch the insides of the cylinder easily.



You can check out the demonstration video for the product from this QR code.



| Wire dia. (φ) | Total length (mm) | Brush length (mm) | Shaft dia. (φ) | Part Number | | Unit Price (1~10 pcs) | |
|---------------|-------------------|-------------------|----------------|-------------|-------------------|-----------------------|------|
| | | | | Type | Brush dia. | M-SC | M-SB |
| 0.25 | 200 | 120 | 6.4 (1/4 NPT) | M-SC | 18 ^(*) | | |
| | | | | | 19 ^(*) | | |
| | | | | | 22 ^(*) | | |
| | | | | | 24 ^(*) | | |
| | | | | | 25 | | |
| | | | | | 27 ^(*) | | |
| | | | | | 28 ^(*) | | |
| | | | | | 30 ^(*) | | |
| | | | | | 32 | | |
| | | | | | 35 ^(*) | | |
| 0.3 | 200 | 120 | 6.4 (1/4 NPT) | M-SB | 36 ^(*) | | |
| | | | | | 38 | | |
| | | | | | 40 ^(*) | | |
| | | | | | 42 ^(*) | | |
| | | | | | 45 | | |
| | | | | | 50 | | |
| | | | | | 54 ^(*) | | |
| | | | | | 55 ^(*) | | |
| | | | | | 57 | | |

| Wire dia. (φ) | Total length (mm) | Brush length (mm) | Shaft dia. (φ) | Part Number | | Unit Price (1~10 pcs) | |
|---------------|-------------------|-------------------|----------------|-------------|--------------------|-----------------------|------|
| | | | | Type | Brush dia. | M-SC | M-SB |
| 0.3 | 200 | 120 | 6.4 (1/4 NPT) | M-SC | 60 ^(*) | | |
| | | | | | 64 ^(*) | | |
| | | | | | 65 ^(*) | | |
| | | | | | 69 ^(*) | | |
| | | | | | 70 | | |
| | | | | | 75 ^(*) | | |
| | | | | | 76 ^(*) | | |
| | | | | | 80 ^(*) | | |
| | | | | | 83 ^(*) | | |
| | | | | | 89 ^(*) | | |
| 0.46 | 200 | 120 | 6.4 (1/4 NPT) | M-SB | 90 ^(*) | | |
| | | | | | 95 ^(*) | | |
| | | | | | 102 ^(*) | | |
| | | | | | 105 ^(*) | | |
| | | | | | 114 ^(*) | | |
| | | | | | 115 ^(*) | | |
| | | | | | 133 ^(*) | | |
| | | | | | 135 ^(*) | | |
| | | | | | 152 ^(*) | | |

- Ⓜ (*) is Type: M-SC only
- Ⓜ (**) is Type: M-SB only
- Ⓜ The brush diameter displayed is made 0.1-0.2 mm bigger, select a suitable brush based on the cylinder's inner diameter.
- Ⓜ For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number

M-SC-18
M-SB-19



Days to Ship

Quotation




Price

Quotation

■ Application Use for cleaning cylinders.

■ Features

- Extension shaft to be connected to cylinder brush.



| Total length (mm) | Fitting inner dia. | Maximum dia. (φ) | Material | Part Number | Unit Price (1~4 pcs) |
|-------------------|--------------------|------------------|-------------|-------------|----------------------|
| 960 | 1/4 NPT | 19 | Glass fiber | M-WES-G | |
| | | | Steel | M-WES-S | Quotation |
| 1220 | | | Glass fiber | M-WESL-G | |
| | | | Steel | M-WESL-S | |

Ⓜ For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number

M-WES-S
M-WESL-G



Days to Ship

Quotation



Price

Quotation