


JOINTS FOR COOLING WATER

-PLUGS-


Matching Joint Plug Connections P.245 Guide for Socket · Plugs P.247 · 248

RoHS 10



LJPJH (Hexagonal head long type)

※Socket connection section




Matching Sockets: **P.257**

Thread JIS B0203 tapered thread for tubing R(PT)

M Brass (C3604)

Matching Sockets: **P.257**



RoHS 10

LJPJ (Hexagonal hole long type)

※Socket connection section

Allen wrenching hole on both ends (socket connection and tapered thread parts). The hex-wrench hole extends to a point mid-way from both ends. It is not fully pierced.

Thread JIS B0203 tapered thread for tubing R(PT)


M Brass (C3604)

Max. pressure MPa (kgf/cm ²)	Matching sockets	Socket connection parts		D1	D2	d	Tapered thread R(PT)		Opposite side Nominal dia.		Part Number		L	
		V	ℓ				R(PT)	ℓ1	Type	No.				
1.0 (10)	Cooling Joint Series Socket hole diameter V=9.4	9.4	10.4	12	10	5.8	1/8	9	6A	1/8	Hexagonale head, long	1	100 110 120 130 140 150 200	
				14	13.2		1/4	11	8A	1/4	LJPJH (Brass)	2		
		9.4	10.4	14	10	1/8	9	6A	1/8	Hexagonale hole, long	1	40~115 (5 mm increments)		120~200 (10 mm increments)
				13.2	1/4	11	8A	1/4	LJPJ (Brass)	2				

Part Number		Unit Price (1~9 pcs)							
Type	No.	L	L100	L110	L120	L130	L140	L150	L200
LJPJH	1								
	2				Quotation				


Part Number		Unit Price (1~9 pcs)				
Type	No.	L	L40~60	L65~100	L105~150	L160~200
LJPJ	1					
	2				Quotation	

RoHS 10



JPLJM
(L-shaped swivel type)
(-Constant flow type-)


※Socket connection section



Refer to **P.252** on the difference of inner structure of swivel type.

JPLJ
(L-shaped swivel type)

※Socket connection section



Hexagonal hole bored at the tapered screw end.

Matching Sockets: **P.257**

JPLJM
M Body: Brass (C3604)
Inner parts: Brass (C2700W)
Fluoric rubber
Fluoric rubber grease

JPLJ
M Brass (C3604)
Thread JIS B0203
Tapered thread for tubing R(PT)

Max. pressure MPa (kgf/cm ²)	Matching sockets	Socket connection parts		L	L2	Allen side B	Hexagonal wrench socket d	Tapered thread R(PT)	ℓ1	Opposite side Nominal dia.		Part Number		Unit Price 1~9 pcs
		V	ℓ							Type	No.			
1.0 (10)	Cooling Joint Series Socket hole diameter V=9.4	9.4	10.4	35.5	16.5	20	φ6	1/8	9.5	6A	1/8	L-shaped swivel type	1	Quotation
				38.5			1/4	12.5	8A	1/4	JPLJM (Brass)	2		
		9.4	10.4	36.5	15.75	19	φ5	1/8	9.5	6A	1/8	L-shaped swivel type	1	
				39.5			1/4	12.5	8A	1/4	JPLJ (Brass)	2		

These plugs are applicable to slim design sockets. P.257

Order

Part Number — **L**

LJPJ 2 — 100

JPLJ 1

Days to Ship

Quotation

Price

Quotation

ex Example

As for L-Shaped Swivel Plugs, the tube extraction angle can be altered by turning its head after tightening the screw.

Note that intermittent or continuous turning of the head could damage the O-ring, which results in water leakage.

