

MOUNTING CLAMP


FRAME HOLDER (FOR SQUARE FRAME)

AT-FRCL (Flat frame type)

■ D (5.5/6.6) Mounting

■ D (9) Mounting

Type	Material	Surface treatment
AT-FRCL	A6061 equivalent	White alumite



■ Mounting Clamp

Connection frame	A	B	C	E	F	D1	G	H	J	K	Flat frame fixing bolt	Weight (g)*1	Part Number Type	Mounting hole size D	Mounting bolt	Unit price 1~10 pcs
HF5FINS-1020 (Flat frame)	36	20	31	21	5.5	14	9	—	—	15	M5 length 14 1 pc (Accessories)	25	AT-FRCL 1020	5.5	BPT5	Quotation
	38	20	32	21	6.6	14	12	—	—	15		25		6.6		
	40	24	32.5	21	6.6	14	12	—	—	15		27		9		

■ Mounting Clamp (Mounting Bolt Set)

Part Number Type	No.	Mounting hole size D	Mounting bolt	Unit price 1~10 pcs
AT-FRCL 1020	5.5	6.6	BPT5	Quotation
	6.6	9	BPT12	
	9			

*1 The weight is an approximate value. Consider it a guideline.

Please check with our WOS for the purchase order that exceeds the displayed quantity.

Please check with our WOS for the purchase order that exceeds the displayed quantity.

■ Bolt Set Details

Mounting clamp model (Mounting bolt set)	Applicable base plate (AT-BPL) Thickness T	Mounting bolt details
AT-FRCL1020-D5.5-BPT5	5 (AT-BPL□□-T5)	M5×P0.8-25 (CB5-25) : 1 pc
AT-FRCL1020-D6.6-BPT5		M6×P1.0-25 (CB6-25) : 1 pc
AT-FRCL1020-D9-BPT5		M8×P1.25-25 (CB8-25) : 2 pcs
AT-FRCL1020-D5.5-BPT12	12 (AT-BPL□□-T12)	M5×P0.8-30 (CB5-30) : 1 pc
AT-FRCL1020-D6.6-BPT12		M6×P1.0-30 (CB6-30) : 1 pc
AT-FRCL1020-D9-BPT12		M8×P1.25-30 (CB8-30) : 2 pcs




Part Number — D — Mounting bolt
 AT-FRCL1020 — D5.5 — BPT5
 AT-FRCL1020 — D6.6 — BPT12



Quotation

AT-FRCLS (20 mm square frame type)

Type	Material	Surface treatment
AT-FRCLS	A6061 equivalent	White alumite



■ Mounting Clamp

Connection frame	A	B	C	E	F	G	J	D1	K	Bolt for fixing square aluminum frame	Weight (g)*1	Part Number Type	Mounting hole size D	Mounting bolt	Unit price 1~10 pcs
HF5S-2020 (Square aluminum frame)	36	20	20	18	22	9.5	5.4	5.5	6	M5 length 20 2 pcs (Accessories)	36	AT-FRCLS 2020	5.5	BPT5	Quotation
	36	20	20	18	22	9.5	5.4	5.5	6		6		6.6		
	38	20	20	18	22	9.5	5.4	5.5	6		7		9		

■ Mounting Clamp (Mounting Bolt Set)

Part Number Type	No.	Mounting hole size D	Mounting bolt	Unit price 1~10 pcs
AT-FRCLS 2020	5.5	6.6	BPT5	Quotation
	6.6	9	BPT12	
	9			

*1 The weight is an approximate value. Consider it a guideline.

Please check with our WOS for the purchase order that exceeds the displayed quantity.

Please check with our WOS for the purchase order that exceeds the displayed quantity.

■ Bolt Set Details

Mounting clamp model (Mounting bolt set)	Applicable base plate (AT-BPL) Thickness T	Mounting bolt details
AT-FRCLS2020-D5.5-BPT5	5 (AT-BPL□□-T5)	M5×P0.8-25 (CB5-25) : 1 pc
AT-FRCLS2020-D6.6-BPT5		M6×P1.0-25 (CB6-25) : 1 pc
AT-FRCLS2020-D9-BPT5		M8×P1.25-25 (CB8-25) : 1 pc
AT-FRCLS2020-D5.5-BPT12	12 (AT-BPL□□-T12)	M5×P0.8-30 (CB5-30) : 1 pc
AT-FRCLS2020-D6.6-BPT12		M6×P1.0-30 (CB6-30) : 1 pc
AT-FRCLS2020-D9-BPT12		M8×P1.25-30 (CB8-30) : 1 pc



Part Number — D — Mounting bolt
 AT-FRCLS2020 — D5.5 — BPT5
 AT-FRCLS2020 — D6.6 — BPT12



Quotation

AT-FRHC

■ D1 (10 · 15) Mounting

■ D1 (20) Mounting

Type	Material	Surface treatment
AT-FRHC	A6061 equivalent	White alumite

When clamping the shaft, tighten with a slit of under 1 mm as a guide.

Connection frame	A	B	C	E	F	G	H	J	K	D	Weight (g)*1	Supplied bolts	Part Number		Unit price 1~10 pcs
													Type	D1	
HF5FINS-1020 HF5S-2020	52	14						36	—		28	M4-8: 1 pc M5-14: 1 pc	AT-FRHC	10	Quotation
														15	
HF5S-2020	60	20	20	15	21	14	9	39	—	5.5	48	M5-12: 1 pc M5-14: 1 pc M6-15: 1 pc M5-14: 2 pc	AT-FRHC	15	Quotation
														20	
														20	

*1 The weight is an approximate value. Consider it a guideline.

Please check with our WOS for the purchase order that exceeds the displayed quantity.




Part Number
AT-FRHC20




Quotation



Example



The slide/height can be adjusted.



As the suction bracket is fixed directly to the frame holder, it can be finished compactly.