

OIL-FREE SLIDE PLATES

— COPPER ALLOY 10mm TYPE —

OIL-FREE THIN SLIDE PLATES

— COPPER ALLOY 5mm TYPE —

STLW • W=35 · 50

• Slide direction

• W=75

• Mounting bolts
Short hexagon socket head cap screw M8×15

■ Copper alloy
Special solid lubricant (embedded)

Location of mounting bolt	Qty. of mounting bolt	Catalog No.	W	(L)
ℓ	ℓ ₁			
60	—	STLW	35	100
55	50			150
70	70			200
65	65			250
80	75			300
60	—		50	100
55	50			150
70	70			200
65	65			250
80	75			300
110	—	75	150	
80	—		200	
105	—		250	
85	90		300	
120	120		400	
115	—	500		

Order **STLW** 35 — 200

Days to Ship **Quotation**

Price **Quotation**

UTW RoHS

• Slide direction

• Provided mounting bolts

■ Copper alloy
Special solid lubricant (embedded)

▲ Special flush hexagon socket head cap screws

ℓ	ℓ ₁	d	d ₁	h	Mounting hole	Mounting bolt	Catalog No.	W	L
20	—	6.5	13.5	1.5	2 holes	M6	UTW	18	50
45	—								75
70	—								100
60	—	10	18	0.8	2 holes	M8		28	50
45	—								75
70	—								100
60	—	10	18	0.8	3 holes	M8		38	50
45	—								75
70	—								100
60	—	10	18	0.8	3 holes	M8		75	50
45	—						75		
70	—						100		
60	—	10	18	0.8	4 holes	M8	100	50	
45	—							75	
70	—							100	
60	—	10	18	0.8	6 holes	M8	100	50	
45	—							75	
70	—							100	
60	—	10	18	0.8	4 holes	M8	100	50	
45	—							75	
70	—							100	
60	—	10	18	0.8	6 holes	M8	100	50	
45	—							75	
70	—							100	

Order **UTW** 75 — 100

Days to Ship **Quotation**

Price **Quotation**