

OIL-FREE SLIDE PLATES

— COPPER ALLOY L-SHAPE TYPE —

OIL-FREE SLIDE PLATES

— COPPER ALLOY BLANK TYPE —

STLST

• Slide direction

☑ Copper alloy
Special solid lubricant (embedded at /// parts)

Specification	Mounting bolt		Location of mounting bolt		Catalog No.	(W)	(L)	
	Qty.		ℓ	ℓ ₁				
M8	2		60	—	STLST	26	100	
	3		55	—			150	
	4		50	50			200	
M10	2		60	—		32	50	100
	3		55	50				150
	4		70	70				200
			55	50	250			
			70	70	200			
	5		65	65	300			
		80	75	350				

Order **Catalog No.** **(W)** — **(L)**
STLST 26 — 150

Days to Ship **Quotation**

Price **Quotation**

STBW

• Slide direction

• When using

- Please cut it to the desired length before using.
- Please drill mounting bolt holes before using.
- Please leave the machining allowance of 0.3mm.

☑ Copper alloy
Special solid lubricant (embedded)

Recommended bolt	Catalog No.	W	L	T
M6×10 Small flush head screw	STBW	20	305	5
		25		
		30		
M8×15 Hexagon socket head cap screw		35	605	10
		40		
		50		
M10×20 Hexagon socket head cap screw	60		15	

Order **Catalog No.** **W** — **L** — **T**
STBW 20 — 305 — 5

Days to Ship **Quotation**

Price **Quotation**